

# Product data sheet

Specifications



## Multi9 - C60 UL489 - MCB - 1P - 2 A - D Curve - 277 V - 10 kA - ring term

MGN61401

⚠ Discontinued on: May 7, 2019

⚠ Discontinued

### Main

Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60 UL489
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	2 A at 25 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	D
Breaking Capacity	10 kA AIR at 277 V AC conforming to UL 489 10 kA AIR at 277 V AC conforming to CSA C22.2 No 5.2 10 kA Icu at 277 V AC conforming to EN/IEC 60947-2 10 kA Icu at 277 V AC conforming to GB 14048.2
Suitability For Isolation	Yes conforming to EN/IEC 60947-2

### Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	277 V AC
Magnetic Tripping Limit	12 x In +/- 20 % AC
Limitation Class	3 conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	141 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	18 mm
Depth	68.7 mm
Net Weight	0.11 kg
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Ring terminal (top or bottom)
Tightening Torque	2 N.m top or bottom

## Environment

Standards	GB 14048.2 EN/IEC 60947-2 UL 489 CSA C22.2 No 5
Product Certifications	CSA CCC IEC UL
Ip Degree Of Protection	IP40 (modular enclosure) conforming to IEC 60529 IP10 conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...80 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.501 cm
Package 1 Width	1.801 cm
Package 1 Length	14.1 cm
Package 1 Weight	163.293 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

## Certifications & Standards

**Eu Rohs Directive** Compliant  
[EU RoHS Declaration](#)

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

**Weee** The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins