



Main

Range of product	Unica
Aesthetic name	Unica Top - Unica Class
Device application	Control
Product or component type	Switch
Device presentation	Mechanism
Switch function	1-pole 1-way
Colour tint	Aluminium

Complementary

Rated current	10 A, 250 V AC, 50/60 Hz
Electrical durability	40000 cycles (cos phi: 0.6)
Insulation resistance	> 5 MOhm @500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi: 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	1 module
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm ² (rigid) 0...2.5 mm ² (flexible)
Material	Mechanism cover : ASA + PC Mechanism cover : ABS (acrylonitrile butadiene-styrene)
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	33 mm
Embedding depth	21 mm

Product weight	0.0194 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach Acetone Petrol Ammonia Window-cleaning fluid Liquid soap Oil Alcohol UV resistant
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0622 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------