

Product data sheet

Specifications



Marisio Habit-21 - pushbutton switch - 3 modules - 1-way - 16A 250VAC - black

MWD082046825

⚠ Discontinued on: Dec 15, 2022

⚠ Discontinued

Main

Range Of Product	Marisio Habit-21
Product Or Component Type	Push-button switch
Device Presentation	Mechanism
Colour Tint	Black
Type Of Packing	Flow-pack

Complementary

Device Mounting	Flush
Number Of Modules	3 modules
Switch Function	1-way
Actuator	Push-button
Rated Current	16 A
[Ue] Rated Operational Voltage	250 V AC
Fixing Mode	Clip-in
Material	PC (polycarbonate)
Surface Finish	Rugous
Connections - Terminals	Screw clamp terminal
Awg Gauge	AWG 12
Embedding Depth	27 mm
Projecting Depth	15 mm
Width	75 mm
Height	45 mm
Depth	42 mm
Net Weight	0.038 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	1.3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	2.7 cm
Package 1 Weight	500 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations