


# Product data sheet

Specifications



## Unica KNX - push-button - 2-way - 10 A 24 V DC - 2 m - graph.

MGU3.530.12

⚠ Discontinued on: Sep 30, 2023

⚠ Discontinued

### Main

Range Of Product	Unica
Aesthetic Name	Unica KNX
Product Or Component Type	Push-button
Device Presentation	Mechanism
Technology Type	Electronic
Bus Type	KNX
Switch Function	1-pole 2-way
Number Of Rocker	1
Device Application	Light control
Colour Tint	Graphite

### Complementary

Rated Current	10 A
[Ue] Rated Operational Voltage	24 V
Network Type	DC
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Actuator	Push-button
Number Of Modules	2 modules
Pilot Light	LED, colour: blue, current consumption: 1 mA, temperature rise: 15 °C
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	Plastic
Surface Finish	Varnished
Device Mounting	Flush
Fixing Mode	Clip-in
Depth	38 mm
Embedding Depth	13 mm
Ambient Air Temperature For Operation	-5...45 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1 LV directive EMC directive
-----------	---

## Environment

Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Oil UV resistant Alcohol Window-cleaning fluid Bleach Acetone Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	93.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.74 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>