


Product data sheet

Specifications



Actassi - side panel - 24U - depth 600 mm

NSY2PLVDC24U6N

 **Discontinued on:** Dec 3, 2020

 **Discontinued**

Main

Range Of Product	Actassi
Product Or Component Type	Side panel
Accessory / Separate Part Category	Cladding accessory
Type Of Paint	Textured
Colour	Black (RAL 9011)
Quantity Per Set	Set of 2

Complementary

Device Composition	Plastic obturator Ventilation louvres
Product Compatibility	Keylock NSYSTVDA
Material	Sheet steel
Surface Finish	Epoxy-polyester powder
Thickness	50 mm
Range Compatibility	Actassi VDS Actassi VDA
Product Destination	Enclosure
Number Of Rack Unit	24U
Height	1200 mm
Depth	600 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	50.5 cm
Package 1 Width	2 cm
Package 1 Length	120 cm
Package 1 Weight	1.3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile