

# Product data sheet

Specifications



## ClimaSys forced vent. IP54, 85m3/h, 115V, with outlet grille and filter G2

NSYCVF85M115PF

### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 79 m3/h at 50 Hz Free flow rate with standard filter: 92 m3/h at 60 Hz
[Us] Rated Supply Voltage	75...126 V
Input Voltage	115 V 50/60 Hz

### Complementary

Absorbed Power	15 W 60 Hz 16 W 50 Hz
[In] Rated Current	0.207 A 50 Hz 0.179 A 60 Hz
Noise Level < At	46...49 dB
Bearing Type	Ball
Height	External: 170 mm
Width	External: 150 mm
Depth	62 mm external:
Cut-Out Dimensions	125 x 125 mm
Net Weight	0.78 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Maximum Pressure	50 Pa flow rate 0 m³/h
Connections - Terminals	Faston connector
Ip Degree Of Protection	IP54
Device Composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template 1 power cord

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Condition Of Use	Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Outside temperature must be 5 °C lower than inside temperature Flow rates depends on the work point, see ProClima software Filter must be cleaned and replaced regularly
------------------	---

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	15.5 cm
Package 1 Length	18.5 cm
Package 1 Weight	915 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	21 cm
Package 2 Width	33 cm
Package 2 Length	43 cm
Package 2 Weight	9.526 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	240
Package 3 Height	105 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	242 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)