


# Product data sheet

Specifications



One entry cable gland plate,  
PanelSeT SFN, Spacial SF, for  
electrical enclosure W1000  
D800mm, fixed by clips

NSYEC1081

## Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial SF
Mounting Location	Enclosure bottom
Cable Gland Type	Standard
Cable Entry	1 entry
Device Composition	fixing elements 1 plate self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity Per Set	Set of 1
Material	Galvanised steel

## Complementary

Height	30 mm
Width	Nominal: 1000 mm Useful: 816 mm
Depth	800 mm nominal:
Thickness	1.5 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	35.0 cm
Package 1 Length	85.0 cm
Package 1 Weight	8.536 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	40
Package 2 Height	80.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	354.0 kg
------------------	----------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations