

Product data sheet

Specifications



Wall mounted steel enclosure,
Spacial S3D, plain door, with
mounting plate, 1000x800x400mm,
IP66, IK10

NSYS3D10840P

Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	400 mm
Door Type	Plain
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 2 cable gland plate 1 mounting plate 1 door with lock

Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure: steel Mounting plate: galvanised steel
Surface Finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
Product Certifications	GL BV UL DNV LR cUL

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	57 kg
------------	-------

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	45.5 cm
Package 1 Width	82.5 cm
Package 1 Length	102.5 cm
Package 1 Weight	55.2 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	4
Package 2 Height	179.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	238.3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations