

Product data sheet

Specifications



Spacial SD Control desk with console & mounting plate - H1400xW800xD845 - IP55

NSYSDF88P

⚠ Discontinued

Main

| | |
|----------------------|---|
| Range | Spacial |
| Product Name | Spacial SD |
| Enclosure Type | Multi-purpose |
| Category | Control desk with console and desk |
| Nominal Height | 1400 mm |
| Nominal Width | 800 mm |
| Nominal Depth | 845 mm |
| Product Installation | Floor-standing |
| Device Composition | 1 structure 4 adjustment rail 1 cable gland plate 2 pneumatic stay: desk lid 1 front console door 1 desk lid 1 front door 1 rear door 2 mechanical stay: front console door 6 lock: front door 1 handle lock: rear door 1 mounting plate: lower part |

Complementary

| | |
|-----------------------------|--|
| Body Type | Single piece structure folded and welded |
| Door Type | Plain |
| Number Of Doors | Front: 1 door(s) Rear: 1 door(s) |
| Door Opening Side | Reversible 120 ° front and rear doors Folding 75 ° desk lid and console cover |
| Lock Type | Handle lock, 5 mm double bar 2 points lock, 3 mm double-bar |
| Mounting Plate Description | Plain |
| Type Of Gland Plate | 1 entry plate |
| Accessibility For Operation | Front Rear |
| Removable Parts | Desk lid by hinges Cable gland plate by clipping screws Mounting plate by mounting plate brackets Front door by hinges Front console door by hinges Rear door by hinges |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------|------------------------|
| Material | Body: steel |
| Surface Finish | Epoxy-polyester powder |
| Thickness | 1.5 mm |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|