



## Main

Range	Linery
Product name	Linery TR
Product or component type	Terminal block
Device short name	TRR
Accessory / separate part category	Connection accessory
Terminal block type	Passthrough
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	2.5 mm <sup>2</sup>
Length	48.5 mm
Colour	Grey
Quantity per set	Set of 50

## Complementary

Width	5.2 mm
Height	36.5 mm
Connections - terminals	1 x spring terminal : upstream 1 x spring terminal : downstream
Number of connections	2
Connection position	Top
Number of measurement input	2
Cable cross section	0.08...2.5 mm <sup>2</sup> , flexible without cable end 0.08...4 mm <sup>2</sup> , solid with cable end 0.2...2.5 mm <sup>2</sup> , flexible with cable end 0.08...4 mm <sup>2</sup> , solid without cable end
Wire stripping length	10 mm
Tool type	Connection : flat screwdriver Disconnection : flat screwdriver
[Ue] rated operational voltage	600 V CSA 600 V cURus 800 V conforming to EN/IEC 60947-7-1
[In] rated current	24 A conforming to EN/IEC 60947-7-1 20 A CSA 20 A cURus

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Polyamide 6/6 (insulating case) Copper alloy (connector and screw) Copper alloy (commoning link) Chromium-nickel steel (spring)
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 M $\Omega$ .m conforming to IEC 60093 10000 M $\Omega$ .m conforming to VDE 0303-T30
Surface resistance	1000 G $\Omega$ conforming to IEC 60093 1000 G $\Omega$ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Product weight	5.6 g
Range compatibility	Prisma - G Prisma - P Pragma Prisma - PH Prisma - Pack Spacial Kaedra TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	DNV EAC cURus IEC-Ex VDE ATEX LR GL CSA
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------