



## Main

Range	Linery
Product name	Linery TR
Product or component type	Terminal block
Device short name	TRR
Terminal block type	Protective earth
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	35 mm <sup>2</sup>
Length	100 mm
Colour	Green-yellow
Quantity per set	Set of 50

## Complementary

Width	16 mm
Height	59 mm
Connections - terminals	1 x spring terminal : upstream 1 x spring terminal : downstream
Number of connections	2
Connection position	Top
Number of measurement input	2
Cable cross section	2.5...35 mm <sup>2</sup> , flexible without cable end 2.5...35 mm <sup>2</sup> , solid
Wire stripping length	25 mm
Tool type	Connection : flat screwdriver Disconnection : flat screwdriver
Material	Polyamide 6/6 (insulating case)
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30

Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Product weight	51.2 g
Range compatibility	Prisma - G Prisma - P Prisma - PH Prisma - Pack Spacial Kaedra TeSys
Product compatibility	Spacial enclosures

## Environment

Product certifications	CSA cURus EAC
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21