

# Product data sheet

Specifications



## PowerPacT multistandard - H-Frame - 40 A - 100 KA - Therm-Mag trip unit

NHJF36040TW

❗ Discontinued

### Main

Range Of Product	PowerPacT multistandard
Range	PowerPacT
Product Name	H-Frame
Device Short Name	H-Frame
Product Or Component Type	Circuit breaker
Device Application	Distribution

### Complementary

Poles Description	3P
Control Type	Toggle
Mounting Mode	Unit mount
Mounting Support	Flush Backplate DIN rail
Electrical Connection	Terminal nut, line side Terminal nut, load side
[In] Rated Current	40 A at 40 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489
Breaking Capacity Code	HJ
Suitability For Isolation	Yes
Utilisation Category	Category A
Mechanical Durability	4000 cycles
Electrical Durability	4000 cycles
Connection Pitch	45 mm
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Trip Unit Name	TM
Trip Unit Technology	Thermal-magnetic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Trip Unit Protection Functions</b>	Basic protection
<b>Trip Unit Rating</b>	40 A
<b>Display Type</b>	3 LEDs
<b>Breaking Capacity</b>	Icu: 100 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 65 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 65 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 25 kA at 500/525 V - AC conforming to IEC 947-2 100 kA at 240 V - AC conforming to UL 489 65 kA at 480 V - AC conforming to UL 489 25 kA at 600 V - AC conforming to UL 489
<b>[Ics] Rated Service Breaking Capacity</b>	Ics: 100 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 65 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 65 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 25 kA at 500/525 V - AC conforming to IEC 947-2
<b>Long Time Pick-Up Adjustment Type Ir</b>	Fixed
<b>Long Time Pick-Up Adjustment Range</b>	1 In
<b>Short-Time Pick-Up Adjustment Type Isd</b>	Fixed
<b>[Isd] Short-Time Pick-Up Adjustment Range</b>	850 A
<b>Overvoltage Category</b>	II
<b>Provision For Padlocking</b>	Non padlockable
<b>Height</b>	163 mm
<b>Width</b>	104 mm
<b>Depth</b>	86 mm
<b>Standards</b>	W-C-375B/GEN CSA C22.2 No 5 IEC 60947-2 NEMA AB1 UL 489 NMX J-266
<b>Product Certifications</b>	CE CCC
<b>Net Weight</b>	2.2 kg
<b>Tightening Torque</b>	5 N.m for 2.5...95 mm² (AWG 14...AWG 3/0)

## Environment

<b>Ip Degree Of Protection</b>	IP40 conforming to IEC 60529
<b>Ik Degree Of Protection</b>	IK07 conforming to IEC 62262
<b>Pollution Degree</b>	3 conforming to IEC 60947-1 3 conforming to IEC 60664-1
<b>Ambient Air Temperature For Operation</b>	40 °C
<b>Ambient Air Temperature For Storage</b>	-50...85 °C

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	15.011 cm
<b>Package 1 Width</b>	18.999 cm
<b>Package 1 Length</b>	22.504 cm

---

Package 1 Weight	1.888 kg
------------------	----------

# Sustainability

**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>