

# Product data sheet

Specifications



Circuit breaker, PowerPacT L, 600A, 3 pole, 600VAC, 18kA, busbar, MicroLogic 5.3A, multistandard, metric terminal nut

NLGF36600U53XTW

## Main

Range Of Product	PowerPact multistandard
Range	PowerPact
Product Name	L-Frame
Device Short Name	L-Frame
Product Or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

Poles Description	3P
Control Type	Toggle
Mounting Mode	Unit mount
Mounting Support	Flush DIN rail Backplate
Electrical Connection	Terminal nut, line side Terminal nut, load side
[In] Rated Current	600 A at 40 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489
Breaking Capacity Code	LG
Suitability For Isolation	Yes
Utilisation Category	Category A
Mechanical Durability	5000 cycles
Electrical Durability	1000 cycles
Connection Pitch	45 mm
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Trip Unit Name	MicroLogic 5.3 A
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSI

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Trip Unit Rating	600 A
Thermal Memory	20 mn
Display Type	Digital display
Breaking Capacity	Icu: 65 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 35 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 35 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 18 kA at 500/525 V - AC conforming to IEC 947-2 65 kA at 240 V - AC conforming to UL 489 35 kA at 480 V - AC conforming to UL 489 18 kA at 600 V - AC conforming to UL 489
[Ics] Rated Service Breaking Capacity	Ics: 65 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 35 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 35 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 18 kA at 500/525 V - AC conforming to IEC 947-2
Long Time Pick-Up Adjustment Type Ir	Adjustable 9 settings
Long Time Pick-Up Adjustment Range	0.33...1 x In
[Tr] Long-Time Delay Adjustment Range	0.5 s 16 s 1 s 2 s 4 s 8 s
Short-Time Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Pick-Up Adjustment Range	1.5...9.5 x Ir
[Tsd] Short-Time Delay Adjustment Range	0 s 0.4 s 0.2 s 0.3 s 0.1 s
Instantaneous Pick-Up Adjustment Type Ii	Adjustable 9 settings
Instantaneous Pick-Up Adjustment Range	1.5...11 x In
Overvoltage Category	II
Provision For Padlocking	Non padlockable
Height	340 mm
Width	140 mm
Depth	110 mm
Standards	UL 489 NMX J-266 W-C-375B/GEN NEMA AB1 IEC 60947-2 CSA C22.2 No 5
Product Certifications	CE CCC
Net Weight	6.2 kg

## Environment

Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1 3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	40 °C

Ambient Air Temperature For Storage	-50...85 °C
-------------------------------------	-------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>