


# Product data sheet

Specifications



## Wall rack VDM 17U fix chass D400

NSYVDM17U4F

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial   |
| Product Name                | Spacial VDM   |
| Application                 | Electronic application  |
| Product Or Component Type   | Compact enclosure   |
| Body Type                   | 1-body  |
| Rack Type                   | Fixed   |
| Enclosure Nominal Height    | 800 mm  |
| Enclosure Nominal Width     | 600 mm  |
| Enclosure Nominal Depth     | 400 mm  |
| Installation Accessory Type | Wall-mounting   |
| Product Destination         | Electronics and networks  |
| Device Composition          | 1 cable gland plate: bottom<br>1 body<br>1 door with lock<br>1 19" fixed rack |

### Complementary

|                             |  |
|-----------------------------|--|
| Door Type                   | Glazed   |
| Number Of Doors             | Front face: 1 door(s)                                |
| Door Opening Side           | Reversible (120 °)                                   |
| Lock Type                   | 3 points lock, 3 mm double-bar                       |
| Type Of Gland Plate         | Standard   |
| Number Of Units 19"         | 17   |
| Accessibility For Operation | Front  |
| Removable Parts             | Door by hinges<br>Rack by fixing element             |
| Material                    | Enclosure: steel<br>19" fixed rack: galvanised steel |
| Surface Finish              | Enclosure: epoxy-polyester powder                    |
| Colour                      | Enclosure: grey (RAL 7035)                           |
| Standards                   | IEC 62208  |
| Net Weight                  | 33.3 kg  |
| Width                       | 600 mm   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|        |        |
|--------|--------|
| Height | 800 mm |
| Depth  | 400 mm |

## Environment

|                         |                              |
|-------------------------|------------------------------|
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 83.0 cm |
| Package 1 Width              | 62.0 cm |
| Package 1 Length             | 42.0 cm |
| Package 1 Weight             | 33.3 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                     |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |