



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	10 W
Input voltage	12...24 V DC
Electrical connection	2 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	UL VDE
Material	Extruded aluminium for body Plastic for cover
Height	External: 98 mm
Width	External: 38 mm
Depth	External: 75 mm
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By clips
Mounting support	35 mm DIN rail

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
