



Main

Range	New Unica
Device application	Power supply
Product or component type	Socket-outlet
Aesthetic name	Unica Studio
Device presentation	Complete product
Socket number	2
Outlet poles configuration	2P + E with shutters
Outlet standard	German
Outlet standard description	Side earth

Complementary

Rated current	16 A at 250 V AC
Network frequency	50/60 Hz
Fixing mode	Screws
Colour tint	Anthracite (RAL 7021)
Connections - terminals	Screw terminals
Cable cross section	0...2.5 mm ² cable(s), 2 - cable stiffness: flexible 0...2.5 mm ² cable(s), 2 - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	PC: mechanism cover
Surface finish	Matt
Quantity per set	Set of 1 flow-pack
Standards	IEC 60884-1 UNE 20315-1-1 UNE 20315-1-2 DIN VDE 0620-1
Product certifications	Aenor EAC
Embedding depth	24 mm
Depth	47 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	85 mm
Height	125 mm
Net weight	0.099 kg
Surface treatment	Painted

Environment

Ambient air temperature for operation	-5...35 °C
Ambient air temperature for storage	-5...50 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	UV resistant Petrol Acetone Ammonia Window-cleaning fluid Alcohol Bleach Oil Liquid soap
Environmental health and issues	Halogen free

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins