



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component type	Fan
Range compatibility	Spacial Prisma P Prisma G
Type of filter	G2
Flow rate	Free flow rate with standard filter: 562 m3/h at 50 Hz Free flow rate with standard filter: 586 m3/h at 60 Hz
[Us] rated supply voltage	207...244 V
Input voltage	230 V 50/60 Hz
Certification	CE EAC REACH RoHS EMC directive 89/336 EEC
Additional information	1 line of 10 characters maximum

Complementary

Absorbed power	68 W 50 Hz 85 W 60 Hz
[In] rated current	0.52 A 50 Hz 0.87 A 60 Hz
Noise level < at	59 dB
Bearing type	Ball
Height	336 mm external:
Width	316 mm external:
Depth	161 mm external:
Cut-out dimensions	291 x 291 mm
Net weight	3.480 kg
Material	Outlet grille: injected thermoplastic (PC) Motor support: injected thermoplastic (ASA PC)
Colour	Outlet grille: smoked black (RAL 9005) Motor support: black (RAL 9005)

Ambient air temperature for operation	-15...60 °C
Ambient air temperature for storage	-40...70 °C
Maximum pressure	140 Pa flow rate 0 m³/h
Connections - terminals	Terminal block
IP degree of protection	IP54
Device composition	1 axial motor 1 external protective transparent smoked grille: front 1 smart filter with dust sensor 1 fan sensor ready to be mounted: rear of outlet grille 1 cable gland 1 cut-out template
Condition of use	Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Outside temperature must be 5 °C lower than inside temperature

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins