

Product data sheet

Specifications

Actassi - 19" upright - set of 2 - 12U

NSYOPB12UF



Main

Range Of Product	Actassi
Product Or Component Type	19" upright
Accessory / Separate Part Category	Installation accessory
Provided Equipment	Fixing elements
Quantity Per Set	Set of 2

Complementary

Mounting Location	Enclosure
Range Compatibility	Actassi OPB
Material	2 mm zinc coated sheet steel
Number Of Rack Unit	12U
Net Weight	1.28 kg
Number Of Rack Unit	12U
Permanent Permissible Load	3 kg per unit 50 kg per enclosure

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5.0 cm
Package 1 Length	64.5 cm
Package 1 Weight	1.252 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	29.0 cm
Package 2 Width	37.5 cm
Package 2 Length	120.0 cm
Package 2 Weight	25.04 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations