

# Product data sheet

Specifications



Switch, New Unica, 1-pole 2-way, 10AX, 2 modules, screwless terminals, painted, IP4X, anthracite

NU320354VMC

## Main

Range Of Product	New Unica
Product Or Component Type	Switch
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	1-pole 2-way
Number Of Rocker	1
Device Application	Fan
Colour Tint	Anthracite (RAL 7021)
Type Of Packing	Flow-pack

## Complementary

Rated Current	10 AX
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	20000 cycles, cos phi = 0.6
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	2 modules
Connections - Terminals	Screwless terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing CuZn37: terminals PBT (polybutylene terephthalate) GF30: release button
Marking	Fan symbol
Surface Finish	Glossy
Specific Treatment - Integrated Within The Material	Painted
Fixing Mode	Clip-in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	45 mm
Height	45 mm
Depth	34.25 mm
Embedding Depth	21.15 mm
Net Weight	0.0189 kg
Ambient Air Temperature For Operation	-5...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Standards	EN 60669-1 LV directive EMC directive
Product Certifications	CE AENOR EAC NF VDE
Resistance To Chemical Agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

## Environment

Ip Degree Of Protection	IP4X
Ik Degree Of Protection	IK04
Environmental Characteristic	Oil UV resistant Acetone Liquid soap Window-cleaning fluid Petrol Alcohol Bleach

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	7.7 cm
Package 1 Length	7.8 cm
Package 1 Weight	21.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.9 cm
Package 2 Width	18.5 cm
Package 2 Length	19.0 cm
Package 2 Weight	291.0 g
Unit Type Of Package 3	S02

Number Of Units In Package 3	20
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	902.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH


## Resource performance


 Sustainable Packaging

## Well-being performance

 Reach Free Of Svhc

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations