

# Product data sheet

Specifications



## Thalassa PHD outdoor heavy duty-enclosure H1593 W1250 D420 IP55 anti-postin door

NSYPHDZT15124

### Main

Range	Thalassa
Product	Thalassa PHD
Application	Outdoor heavy duty
Certification	UL conforming to UL 508 A 2007 Bureau Veritas conforming to IEC 61969-3 2011 Bureau Veritas conforming to IEC 61439-5 2010 DEKRA conforming to IEC 62208 2011
Enclosure Type	Multi-purpose
Category	Suitable enclosure
Version	PHDZT
Enclosure Height With Canopy	1593 mm
Canopy Height	38 mm
Enclosure Width	1250 mm
Enclosure Depth	420 mm
Enclosure Mounting	Floor-standing
Device Composition	1 body in polyester double reinforced with fibreglass 2 doors in polyester double reinforced with fibreglass in side by side 1 document pocket in plastic A4 format 1 canopy in polyester reinforced with fibreglass 2 cable gland plate in aluminium 2 door retainer in steel with anti-corrosive coating

### Complementary

Body Type	Sealed assembled body
Door Type	Anti-posting
Number Of Doors	2 door(s)
Door Opening Side	Right and left (120 °)
Lock Type	4 points lock, handle with 1242E key lock and padlock door
Accessibility For Operation	Bottom Front
Maximum Lifting Load	500 kg
Removable Parts	Door by hinges Canopy by fixing element Cable gland plate by fixing element
Material	Polyester double reinforced with fibreglass
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 508 A IEC 61969-3 IEC 61439-5 IEC 62208
Electrical Insulation Class	Class II conforming to IEC 61439-1 2011

## Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Mechanical Robustness	Vandal-proof conforming to EN/IEC 61439-5 version 2010
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Operation	-45...80 °C conforming to IEC 61969-3 class 1
Ambient Air Temperature For Storage	-25...40 °C
Corrosion Withstand	90...100 % conforming to ISO 12944 C4H
Environmental Withstand	Solar radiation: class 1 up to 1120 W/m² conforming to IEC 61969-3:2011 Surrounding air withstand: class 1 up to 180 km/h conforming to IEC 61969-3:2011 Ultraviolet degradation test: class 1 conforming to ISO 4892-2:2013 Formation of ice and frost: class 1 conforming to IEC 61969-3:2011 Fauna and flora withstand: class 1 conforming to IEC 61969-3:2011 : class 1 conforming to IEC 61969-3:2011
Thermal Management Options	Fan: 1500 W for a maximum noise level of 60 dB With external cooling 4000 W Natural: 1468 W at -25 °C Natural: 642 W at 20 °C Natural: 275 W at 40 °C According to cooling architecture 1500 W

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	156.0 cm
Package 1 Width	126.0 cm
Package 1 Length	48.0 cm
Package 1 Weight	96.0 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations

[Circularity Profile](#)