

Product data sheet

Specifications



Guardian - emergency light block - standard - non-maintained - 1 h - 200 lm

OVA41437E

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Exiway
Product Name	Guardian
Product Or Component Type	Emergency light fitting
Device Application	Lighting
Function	Standard
Supply	Non-maintained
Colour	Black
Light Source	Halogen G4 10 W x 2
Light Source Colour	White
Cover Type	Transparent
Number Of Batteries	1 x 6 V 7.2 Ah lead-acid battery
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls Searchlights rotate on their axis from 90° to 45°

Complementary

[Ue] Rated Operational Voltage	200...230 V AC/DC 50 Hz
Power Consumption In Va	30 VA
Current Consumption	130 mA
Electrical Insulation Class	Class II
Autonomy	1 h
Charging Time	12 h
Luminous Flux	Emergency condition: 200 lm
Material	Plastic: housing Plastic: cover
Device Mounting	Surface ceiling Surface wall
Height	297 mm
Width	400 mm
Depth	168 mm
Net Weight	3.4 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	IEC 695-2-1 EN 60695-2-10 EN 60598-2-22 IEC 50-11

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.0 cm
Package 1 Width	31.0 cm
Package 1 Length	41.0 cm
Package 1 Weight	3.5 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	50.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	82.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile