


Product data sheet

Specifications

Spacial SF Standard enlarged roof W800 x D600 mm



NSYRSF86L

Main

Range	Spacial
Offer Type	Spare part
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Roof
Device Application	Multi-purpose
Mounting Location	On top of enclosure
Range Compatibility	Spacial Spacial SF suitable enclosure
Device Composition	1 roof

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - screw type M12 - roof fixing point location By screws - screw type M6 - roof fixing point location
Height	7.5 mm
Width	796 mm
Depth	596 mm
Thickness	1.5 mm
Ip Degree Of Protection	IP55 conforming to IEC 60529 (enclosure protection)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	82.0 cm
Package 1 Length	61.0 cm
Package 1 Weight	6.28 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations