

Product data sheet

Specifications



Evx Ferro - con kit - standard - up to 58 W - in line - 4 Ah

OVA43106E

 **Discontinued on:** Apr 19, 2021

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Ferro
Product Or Component Type	Conversion kit
Device Application	Lighting
Function	Standard
Wiring Device Additional Information	Can be inhibited with rest mode via remote control

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Rated Power In Va	7 VA
Battery Capacity	4 Ah 3.6 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	13 % of nominal flux during 1 h 30 49 W G5 fluorescent FHO T5 13 % of nominal flux during 1 h 38 W GR10q fluorescent GE 18 % of nominal flux during 2 h 30 24 W G5 fluorescent FHO T5 20 % of nominal flux during 1 h 35 W G5 fluorescent FHE T5 23 % of nominal flux during 2 h 21 W G5 fluorescent FHE T5 25 % of nominal flux during 2 h 30 14 W G5 fluorescent FHE T5 7 % of nominal flux during 1 h 30 54 W G5 fluorescent FHO T5 10 % of nominal flux during 1 h 30 32 W G10q 10 % of nominal flux during 1 h 30 36 W 2G11 10 % of nominal flux during 1 h 40 W 2G11 10 % of nominal flux during 1 h 40 W G10q 10 % of nominal flux during 1 h 58 W G13 10 % of nominal flux during 2 h 36 W 2G10 11 % of nominal flux during 1 h 30 18 W G13 11 % of nominal flux during 2 h 32 W Gx24q 12 % of nominal flux during 1 h 30 26 W G24q 12 % of nominal flux during 1 h 36 W G13 14 % of nominal flux during 1 h 30 18 W G24q 18 % of nominal flux during 1 h 30 18 W 2G11 18 % of nominal flux during 1 h 30 2 x 18 W G13 18 % of nominal flux during 1 h 30 28 W GR10q 25 % of nominal flux during 1 h 30 13 W G24q 25 % of nominal flux during 2 h 2 x 8 W G5 33 % of nominal flux during 2 h 30 11 W 2G7 34 % of nominal flux during 3 h 9 W 2G7 8 % of nominal flux during 1 h 55 W 2G11
Bulb Type	Indicator LED
Ballast Type	Electromagnetic ballast
Electrical Insulation Class	Class II
Connections - Terminals	Screw terminals

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Device Connection	Connection to remote switch
Distance Between Centers	Circuit: 140 mm Battery: 210 mm
Height	Battery: 35 mm Circuit: 32.5 mm
Width	Circuit: 157 mm
Depth	Battery: 39 mm Circuit: 40.5 mm
Net Weight	0.65 kg

Environment

Fire Resistance	850 °C
Standards	IEC 695-2-1 EN 61347-2-7 IEC 34-50 IEC 50-11 EN 60695-2-10 EN 60924

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

[Product Environmental Profile](#)