

Product data sheet

Specifications



Flatbed plotter, Linergy TR, ready to use, A4 format, External supply 100 to 240VAC 50/60Hz, Internal supply 24VDC

NSYTRAPLOT

Main

Range	Linergy
Product Name	TR
Product Or Component Type	Flatbed plotter
Device Short Name	TRA
Accessory / Separate Part Category	Marking accessory

Complementary

Product Compatibility	Legend ZBY HP plotter pen Marking card TRA
[Ue] Rated Operational Voltage	External supply: 100...240 V AC 50/60 Hz Internal supply: 24 V DC
[Ie] Rated Operational Current	external supply: AC 50/60 Hz internal supply: DC
Material	Aluminium
Provided Equipment	Installation guide Power supply USB cable Documentation
Integrated Connection Type	USB port
Label Dimensions	220 x 305 mm
Passing Speed Of Object	40 mm/s
Buffer Size	16 MB
Motor Type	2-phase stepper motor
Repeat Accuracy	+/- 0.05 mm
Height	125 mm
Width	440 mm
Length	440 mm
Net Weight	6 kg
Colour	Grey

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 61000-4-6
	EN 55022 class B
	EN 61000-4-5
	EN 61000-4-2
	EN 61000-4-4
	EN 60950-1
	EN 61000-4-3
	EN 61000-4-11
Ambient Air Temperature For Operation	10...35 °C
Ambient Air Temperature For Storage	-10...50 °C
Relative Humidity	35...75 % in operation
	10...90 % in storage

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	56.0 cm
Package 1 Length	56.0 cm
Package 1 Weight	9.5 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov