


Product data sheet

Specifications



Evx Power - con kit - standard - up to 58 W - in line - 4.5 Ah

OVA43108E

 **Discontinued on:** Dec 31, 2015

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Power
Product Or Component Type	Conversion kit
Function	Standard
Wiring Device Additional Information	Can be inhibited with rest mode via remote control

Complementary

[Ue] Rated Operational Voltage	230/240 V 50 Hz +/- 10 %
Rated Power In Va	6 VA
Battery Capacity	4.5 Ah 4.8 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	12 % of nominal flux during 5 h 14 W G5 fluorescent T5 GE 12.1 % of nominal flux during 20 h 14 W G5 fluorescent FHE T5 13.8 % of nominal flux during 3 h 30 21 W G5 fluorescent FHE T5 5.3 % of nominal flux during 3 h 30 38 W GR10q fluorescent GE 6.1 % of nominal flux during 3 h 40 W 2G11 Philips 6.9 % of nominal flux during 3 h 39 W G5 fluorescent FHO T5 7 % of nominal flux during 4 h 24 W G5 fluorescent FHO T5 12 % of nominal flux during 6 h 10 W G24q 13 % of nominal flux during 5 h 10 W GR10q 13.3 % of nominal flux during 6 h 9 W 2G7 13.7 % of nominal flux during 4 h 16 W GR10q 14.6 % of nominal flux during 5 h 13 W G24q 16.4 % of nominal flux during 5 h 11 W 2G7 3 % of nominal flux during 3 h 55 W GR10q 4.7 % of nominal flux during 4 h 36 W 2G10 4.9 % of nominal flux during 3 h 55 W 2G11 5 % of nominal flux during 3 h 30 38 W GR10q 5.1 % of nominal flux during 3 h 58 W G13 5.3 % of nominal flux during 3 h 30 36 W 2G11 5.5 % of nominal flux during 4 h 30 22 W G10q 5.8 % of nominal flux during 4 h 24 W 2G10 5.8 % of nominal flux during 4 h 32 W G10q 6.3 % of nominal flux during 3 h 40 W G10q 6.3 % of nominal flux during 4 h 24 W 2G11 6.6 % of nominal flux during 4 h 18 W G13 6.9 % of nominal flux during 3 h 36 W G13 7 % of nominal flux during 3 h 40 W 2G11 7.1 % of nominal flux during 4 h 28 W GR10q 7.4 % of nominal flux during 3 h 42 W Gx24q 7.8 % of nominal flux during 3 h 30 32 W Gx24q 8 % of nominal flux during 4 h 26 W G24q 9.4 % of nominal flux during 4 h 18 W G24q 9.4 % of nominal flux during 4 h 18 W Gx24q

Bulb Type	Indicator LED
-----------	---------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ballast Type	Electromagnetic ballast Electronic ballast
Electrical Insulation Class	Class II
Connections - Terminals	Quick-connect terminal strips
Distance Between Centers	Circuit: 220 mm Battery: 275 mm
Height	Circuit: 28 mm Battery: 35 mm
Width	Circuit: 230 mm
Depth	Battery: 39 mm Circuit: 40 mm
Net Weight	0.76 kg

Environment

Fire Resistance	850 °C
Standards	IEC 695-2-1 EN 61347-2-7 IEC 34-50 IEC 50-11 EN 60695-2-10 EN 60924

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	7.3 cm
Package 1 Length	34.3 cm
Package 1 Weight	0.75 kg

Contractual warranty

Warranty	18 months
----------	-----------