


Product data sheet

Specifications



Evx Power - con kit - standard - up to 70 W - in line - 4.5 Ah

OVA43109E

 **Discontinued on:** Dec 31, 2015

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Power
Product Or Component Type	Conversion kit
Function	Standard
Wiring Device Additional Information	Can be inhibited with rest mode via remote control

Complementary

[Ue] Rated Operational Voltage	230/240 V 50 Hz +/- 10 %
Rated Power In Va	6.5 VA
Battery Capacity	4.5 Ah 6 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	10 % of nominal flux during 25 h 14 W G5 fluorescent FHE T5 14.7 % of nominal flux during 4 h 21 W G5 fluorescent FHE T5 15 % of nominal flux during 3 h 28 W G5 fluorescent FHE T5 16 % of nominal flux during 3 h 28 W G5 fluorescent T5 GE 5.5 % of nominal flux during 3 h 40 W 2G11 fluorescent GE 6.6 % of nominal flux during 3 h 54 W G5 fluorescent FHO T5 6.6 % of nominal flux during 4 h 39 W G5 fluorescent FHO T5 7 % of nominal flux during 5 h 24 W G5 fluorescent FHO T5 16.3 % of nominal flux during 5 h 16 W GR10q 4 % of nominal flux during 3 h 30 55 W GR10q 5.6 % of nominal flux during 3 h 70 W G13 5.8 % of nominal flux during 3 h 30 58 W G13 5.8 % of nominal flux during 4 h 36 W 2G10 6 % of nominal flux during 5 h 24 W 2G10 6.5 % of nominal flux during 4 h 36 W 2G11 6.8 % of nominal flux during 4 h 32 W G10q 6.8 % of nominal flux during 5 h 24 W 2G11 7 % of nominal flux during 4 h 55 W 2G11 7.5 % of nominal flux during 5 h 22 W G10q 8 % of nominal flux during 3 h 38 W GR10q 8 % of nominal flux during 4 h 40 W 2G11 8 % of nominal flux during 4 h 40 W 2GX13 8 % of nominal flux during 4 h 40 W G10q 8.1 % of nominal flux during 4 h 32 W Gx24q 8.1 % of nominal flux during 5 h 18 W G13 8.3 % of nominal flux during 3 h 42 W Gx24q 8.3 % of nominal flux during 4 h 36 W G13 8.5 % of nominal flux during 4 h 26 W G24q 8.8 % of nominal flux during 4 h 26 W Gx24q 8.9 % of nominal flux during 4 h 28 W GR10q 9.4 % of nominal flux during 5 h 18 W G24q 9.4 % of nominal flux during 5 h 18 W Gx24q
Bulb Type	Indicator LED
Ballast Type	Electromagnetic ballast Electronic ballast

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Insulation Class	Class II
Connections - Terminals	Quick-connect terminal strips
Distance Between Centers	Circuit: 220 mm Battery: 332 mm
Height	Circuit: 28 mm Battery: 35 mm
Width	Circuit: 230 mm
Depth	Battery: 39 mm Circuit: 40 mm
Net Weight	0.85 kg

Environment

Fire Resistance	850 °C
Standards	IEC 695-2-1 EN 61347-2-7 IEC 34-50 IEC 50-11 EN 60695-2-10 EN 60924

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	7.3 cm
Package 1 Length	34.3 cm
Package 1 Weight	0.948 kg

Contractual warranty

Warranty	18 months
----------	-----------