



### Overview

Description	Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor.
Model Name	InfraStruxure PDU 60kW 208V/208V
Includes	Installation guide , User Manual
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , French Guiana , Haiti , Honduras , Jamaica , Madagascar , Martinique , Mauritius , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , Reunion , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Nominal Output Voltage	120V , 208 3PH
Maximum Total Current Draw per Phase	167 A

### Input

Nominal Input Voltage	208 3PH
Input Frequency	60 Hz +/- 3 Hz
Number of Power Cords	1
Maximum Line Current per phase	167 A

### Physical

Net Weight	460.0 kg
Maximum Height	2057.0 mm
Maximum Width	610.0 mm
Maximum Depth	914.0 mm
Shipping Weight	470.0 kg
Shipping Height	2184.0 mm
Shipping Width	914.0 mm

Shipping Depth	1219.0 mm
Color	Black

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999.9 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters

### Conformance

Approvals	UL 60950
Standard warranty	1 year repair or replace