



Main

Range	Linery
Product name	Linery TR
Product or component type	Terminal block
Device short name	TRV
Terminal block type	Blade disconnect
Terminal block level	2
Mounting mode	Clip-on
Nominal cross section	4 mm ²
Length	69.9 mm
Colour	Grey
Quantity per set	Set of 50

Complementary

Width	6.2 mm
Height	65 mm
Connections - terminals	1 x screw terminal : upstream 1 x screw terminal : downstream
Number of connections	2
Connection position	Sideways
Number of measurement input	2
Cable cross section	0.14...6 mm ² , solid 0.14...6 mm ² , flexible without
Tightening torque	0.6...0.8 N.m
Wire stripping length	9 mm
Tool type	Connection : screwdriver Disconnection : screwdriver
[Ue] rated operational voltage	300 V CSA 300 V cURus 500 V conforming to EN/IEC 60947-7-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[In] rated current	30 A CSA 30 A cURus 30 A conforming to EN/IEC 60947-7-1
Material	Polyamide 6/6 (insulating case)
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m MΩ.m conforming to IEC 60093 10000 MΩ.m MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ GΩ conforming to IEC 60093 1000 GΩ GΩ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Product weight	2.7 g
Range compatibility	Prisma - G Prisma - P Pragma Prisma - PH Prisma - Pack Spacial Kaedra TeSys
Product compatibility	Spacial enclosures

Environment

Product certifications	EAC CSA cURus
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------