



has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range of product	Resi9
Product name	DB60
Product or component type	Circuit-breaker
Device location in system	Main incomer
Pole	1P + N
Maximum current rated	60 A
Settings	45 A 9 kVA 30 A 6 kVA 60 A 12 kVA
Neutral position	Left
Standards	NF C 62-412
Electrical insulation class	Class II
Network type	AC
Trip unit technology	Thermal-magnetic
Safety function	Cover opening open

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC 50 Hz conforming to NF C 62-412
Breaking capacity	2.4 kA
Contact position indicator	Yes
Control type	Toggle
Mounting support	Mounting plate
Height	209 mm
Width	71 mm
Depth	73 mm
Mechanical durability	5000 cycles
Electrical durability	1000 cycles conforming to NF C 62-412

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Provision for padlocking	Yes
Type of connection	Fixed terminal 30°, cable cross section: 1.5...16 mm²
Tightening torque	Setting: 1 N.m Power terminals: 3.5 N.m
Earth-leakage protection	Without

Environment

IP degree of protection	IP40 (front face)
Relative humidity	90 % at 40 °C
Ambient air temperature for operation	-5...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins