



Main

Range	Actassi
Product name	Actassi VDA
Product or component type	19" enclosure
Device application	Cabling
Applications	To protect network connectivity equipment To mount 19" equipment
Enclosure type	Network Cabinet
Front face	Glazed door
Colour	Door : light grey (RAL 7035) Panels : light grey (RAL 7035) Top and bottom : light grey (RAL 7035) Structure : dark grey (RAL 7011)
Back face	Partial plain door
Side face	Panel
Installation mode	Floor-standing

Complementary

Support equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Door type	Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 ° Rear partial plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
Accessibility for operation	Front Rear Side Top
Removable parts	Top blanking plate Bottom blanking plate Front door removable toolless Rear partial door removable toolless Rear partial panel removable toolless
Device composition	1 x front glazed door 1 x assembled structure with CBLX torx screws 1 x top roof with removable blanking plate

	1 x rear partial panel (6U) 1 x rear partial plain door 2 x front 19" uprights 4 x levelling feets
Load rating	Static : 400 kg Dynamic : 250 kg
Number of cut-out	1 cut-out bottom 1 cut-out top - split in 3 parts 1 cut-out top side panel
Material	Panel : sheet steel Structure : sheet steel Door : sheet steel Upright : galvanized steel Door : sekurit glass
Surface finish	Epoxy-polyester powder
Product weight	68 kg
Enclosure nominal dimensions	- 1600 mm 800 mm 600 mm
Number of rack unit	33U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------