

Product data sheet

Specifications



Miniature circuit breaker (MCB), Resi9, 1P, 16A, C curve, 3000A (IEC/EN 60898-1)

R9F64116

Main

Range	Resi9
Product Name	Resi9 MCB
Product Or Component Type	Miniature circuit-breaker
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	16 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	3000 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Standards	EN/IEC 60898-1
Product Certifications	CEBEC

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Magnetic Tripping Limit	5...10 x In
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	440 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Bottom: biconnect
9 Mm Pitches	2
Height	85 mm
Width	18 mm
Depth	75 mm
Net Weight	0.106 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles AC 50/60 Hz conforming to EN/IEC 60898-1
Locking Options Description	Padlock in OFF position
Connections - Terminals	Tunnel type terminals (top or bottom) - <= 35 mm ² - rigid Tunnel type terminals (top or bottom) - <= 25 mm ² - flexible with ferrule Tunnel type terminals (top or bottom) - <= 25 mm ² - flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	2 conforming to EN/IEC 60898-1
Overvoltage Category	III
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	106 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	9 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.322 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	16.351 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Lower Impact Materials Transparency RoHS/REACH

Resource performance

✓ Minimum Percentage Of Recycled Plastic Content 56

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations