



### Main

|                             |   |
|-----------------------------|---|
| Range                       | Spacial                                     |
| Product name                | Spacial VDM                                 |
| Application                 | Electronic application                      |
| Product or component type   | Compact enclosure                           |
| Body type                   | 1-body                                      |
| Rack type                   | Swing                                       |
| Enclosure nominal height    | 500 mm                                      |
| Enclosure nominal width     | 600 mm                                      |
| Enclosure nominal depth     | 400 mm                                      |
| Installation accessory type | Wall-mounting                               |
| Product destination         | Electronics and networks                    |
| Device composition          | 1<br>1<br>1<br>1 bottom<br>2 19" swing rack |

### Complementary

|                             |   |
|-----------------------------|---|
| Door type                   | Glazed  |
| Number of doors             | 1 front face                                  |
| Door opening side           | Reversible 120 °                              |
| Lock type                   | 3 mm double-bar lock                          |
| Type of gland plate         | Standard                                      |
| Number of units 19"         | 9   |
| Accessibility for operation | Front   |
| Removable parts             | Door by hinges<br>Rack by fixing element      |
| Material                    | Steel for enclosure and 19" rack              |
| Surface finish              | Epoxy-polyester powder enclosure and 19" rack |
| Colour                      | Grey RAL 7035 enclosure and 19" rack :        |

|                |           |
|----------------|-----------|
| Standards      | IEC 62208 |
| Product weight | 22.92 kg  |

### Environment

|                         |                              |
|-------------------------|------------------------------|
| IP degree of protection | IP66 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to IEC 62262 |

### Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 0852 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product Environmental Profile</a>  |
| Product end of life instructions | Need no specific recycling operations   |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|