


# Product data sheet

Specifications

Resi9 - comb busbar - 3L+N  
balanced - 18 mm pitch - 57  
modules - 63 A



R9XFH557

## Main

Range	Resi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L + N
Length In 18 Mm Modules	57

## Complementary

Number Of Ways	28 ways N + L
Poles Configuration For 1 Way	1 x 1P + N 1 x 2P
Connection Pitch	18 mm
Connector Type	Fork
Distance Between Way	36 mm
Marking	N L1 N L2 N L3
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	63 A at 40 °C
[Ue] Rated Operational Voltage	230 V AC Ph/N
[Ui] Rated Insulation Voltage	500 V AC
Mounting Location	Bottom on biconnect
9 Mm Pitches	114
Width	1000 mm
Colour	White (RAL 9003)
Range Compatibility	Acti 9 Acti9 K60 Resi9 Resi9 MCB Resi9 Resi9 RCBO Resi9 Resi9 RCCB Resi9 Resi9 SWITCH

## Environment

Standards	IEC 60947-7-1 IEC 61439-2
Product Certifications	CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution Degree	3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	2 cm
Package 1 Length	100 cm
Package 1 Weight	516 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	5.5 cm
Package 2 Width	106.5 cm
Package 2 Length	9 cm
Package 2 Weight	2.754 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	180
Package 3 Height	43 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	112 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations