



Main

Range	Exiway
Product name	Exiway Power Control
Device short name	Exiway Power Control Multi
Product or component type	Central battery system
Number of circuits	72
Number of light blocks	1440
Device composition	battery charger 25 A 36 main circuit module
Supply	Non-maintained Maintained

Complementary

[Us] rated supply voltage	400 V 50 Hz
Poles description	3P
Output voltage	230 V AC 216 V DC
Display type	LCD display
Communication network type	Ethernet TCP/IP
Communication port support	RS485 RS232
Communication port protocol	Modbus
Web services	Web server
Language	Multi-language
Cover type	Lockable cover to be ordered separately
Battery type	Lead-acid battery to be ordered separately
Provided equipment	I/O module internal Battery temperature sensor Centronics printer interface PS/2 keyboard external
Ambient air temperature for operation	0...35 °C
Material	Sheet steel

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Colour	Grey
Colour code	RAL 7035
IP degree of protection	IP20
Mounting mode	Floor-standing
Electrical insulation class	Class I
Standards	DIN VDE 0100-718 EN 55015 EN 50172 EN 61000-3-2 EN 61000-3-3 IEC 60364-5-56 EN 50171 OVE/ONORM E 8002 DIN VDE 0108-100 EN 50272-2 EN 61547
Height	1800 mm
Width	600 mm
Depth	450 mm
Net weight	100 kg