

Product data sheet

Specifications



Evx Power - con kit - adressable - 6 VA - 4.8 V - 4.5 Ah

OVA34216E

⚠ Discontinued on: Dec 31, 2015

⚠ End-of-service on: Dec 17, 2020

⚠ Discontinued

Main

Range	Evx
Aesthetic Name	Evx Power
Product Or Component Type	Conversion kit
Function	Addressable
Wiring Device Additional Information	Can be inhibited with rest mode via Dardo Plus control unit

Complementary

[Ue] Rated Operational Voltage	230/240 V 50/60 Hz +/- 10 %
Rated Power In Va	6 VA
Connections - Terminals	Quick-connect terminal strips
Battery Capacity	4.5 Ah 4.8 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	12.1 % of nominal flux during 5 h 14 W G5 fluorescent FHE T5 13.8 % of nominal flux during 3 h 30 21 W G5 fluorescent FHE T5 6.9 % of nominal flux during 3 h 39 W G5 fluorescent FHO T5 7 % of nominal flux during 4 h 24 W G5 fluorescent FHO T5 12 % of nominal flux during 6 h 10 W G24q 13 % of nominal flux during 5 h 10 W GR10q 13.1 % of nominal flux during 4 h 2 x 8 W G5 13.3 % of nominal flux during 6 h 9 W 2G7 13.7 % of nominal flux during 4 h 16 W GR10q 14.6 % of nominal flux during 5 h 13 W G24q 16.4 % of nominal flux during 5 h 11 W 2G7 4.7 % of nominal flux during 4 h 36 W 2G10 4.9 % of nominal flux during 3 h 55 W 2G11 5.1 % of nominal flux during 3 h 58 W G13 5.3 % of nominal flux during 3 h 30 36 W 2G11 5.5 % of nominal flux during 3 h 30 38 W GR10q 5.5 % of nominal flux during 4 h 30 22 W G10q 5.8 % of nominal flux during 4 h 24 W 2G10 5.8 % of nominal flux during 4 h 32 W G10q 6.3 % of nominal flux during 3 h 40 W G10q 6.3 % of nominal flux during 4 h 24 W 2G11 6.5 % of nominal flux during 3 h 34 W 2G11 6.6 % of nominal flux during 4 h 18 W G13 6.9 % of nominal flux during 3 h 36 W G13 7 % of nominal flux during 3 h 40 W 2G11 7.1 % of nominal flux during 4 h 28 W GR10q 7.4 % of nominal flux during 3 h 42 W Gx24q 7.5 % of nominal flux during 3 h 2 x 18 W G5 7.8 % of nominal flux during 3 h 30 32 W Gx24q 8 % of nominal flux during 4 h 26 W G24q 8 % of nominal flux during 4 h 26 W Gx24q 9.4 % of nominal flux during 4 h 18 W G24q 9.5 % of nominal flux during 4 h 18 W Gx24q
Bulb Type	Indicator LED

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ballast Type	Electronic ballast Electromagnetic ballast
Electrical Insulation Class	Class II
Height	Circuit: 28 mm Battery: 35 mm
Width	Circuit: 234 mm
Depth	Battery: 39 mm Circuit: 40 mm
Distance Between Centers	Circuit: 220 mm Battery: 275 mm
Net Weight	0.76 kg

Environment

Fire Resistance	850 °C
Standards	IEC 60695-2-10 EN 61347-2-7

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8 cm
Package 1 Length	35 cm
Package 1 Weight	0.788 kg

Contractual warranty

Warranty	18 months
----------	-----------