

Product data sheet

Specifications



Quick Signal - emergency exit sign - addressable - maintained - 3 h

OVA34512E

⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

Main

Range	Exiway
Product Name	Quick Signal
Product Or Component Type	Emergency exit sign
Device Application	Signalling
Function	Addressable
Supply	Maintained
Light Source Colour	White
Wiring Device Additional Information	Can be inhibited with rest mode via Dardo Plus control unit Brackets for wall/flag installation included

Complementary

[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	8.5 VA
Current Consumption	17 mA
Visibility Distance	28 m
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Autonomy	3 h
Charging Time	24 h
Bulb Type	LED 100000 h
Luminous Flux	Emergency condition: 12 lm Maintained mode: 14 lm
Electrical Insulation Class	Class II
Device Mounting	Surface ceiling Flush false ceiling Flag type bracket wall Hanging ceiling Surface wall
Height	235 mm
Width	290 mm
Depth	60 mm
Net Weight	0.8 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	EN/IEC 60598-2-22 IEC 695-2-1 IEC 50-11 IEC 60695-2-10 EN 1838

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	25.3 cm
Package 1 Length	32.8 cm
Package 1 Weight	900 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information	