

Product data sheet

Specifications



Rilux - emergency light block - standard - maintained - 3 h - 75/90 lm

OVA37072E

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

Main

Range	Rilux
Product Or Component Type	Emergency light fitting
Device Application	Lighting
Function	Standard
Supply	Maintained
Colour	White
Light Source	Fluorescent tube G5 8 W
Light Source Colour	White
Cover Type	Transparent
Number Of Batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Wiring Device Additional Information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

[Ue] Rated Operational Voltage	200...230 V AC/DC 50 Hz
Power Consumption In Va	10.8 VA
Current Consumption	46 mA
Electrical Insulation Class	Class II
Autonomy	3 h
Charging Time	24 h
Luminous Flux	Emergency condition: 75 lm Maintained mode: 90 lm
Material	Plastic: housing Plastic: cover
Device Mounting	Surface ceiling Surface wall Flush
Height	100 mm
Width	331 mm
Depth	46 mm
Net Weight	0.8 kg
Market Segment	Small commercial

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK06
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	EN 60695-2-10 IEC 695-2-1 IEC 50-11 EN 60598-2-22

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information