

Product data sheet

Specifications



Evx Ferro - con kit - standard - up to 18 W - in line - 2 Ah

OVA43102E

 **Discontinued on:** Dec 31, 2018

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Ferro
Product Or Component Type	Conversion kit
Function	Standard
Wiring Device Additional Information	Can be inhibited with rest mode via remote control

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Rated Power In Va	5 VA
Battery Capacity	2 Ah 3.6 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h
Emergency Luminous Flux	13 % of nominal flux during 1 h 13 W G24q 15 % of nominal flux during 1 h 18 W G13 18 % of nominal flux during 1 h 11 W 2G7 19 % of nominal flux during 1 h 16 W GR10q 20 % of nominal flux during 1 h 10 W G24q 21 % of nominal flux during 1 h 30 9 W 2G7 22 % of nominal flux during 1 h 30 7 W 2G7 24 % of nominal flux during 1 h 30 5 W 2G7 25 % of nominal flux during 1 h 10 W GR10q 25 % of nominal flux during 1 h 13 W G5 25 % of nominal flux during 1 h 30 8 W G5 30 % of nominal flux during 1 h 30 4 W G5 30 % of nominal flux during 1 h 30 6 W G5
Bulb Type	Indicator LED
Ballast Type	Electromagnetic ballast
Electrical Insulation Class	Class II
Connections - Terminals	Screw terminals
Distance Between Centers	Circuit: 140 mm Battery: 165 mm
Height	Battery: 28 mm Circuit: 32.5 mm
Width	Circuit: 157 mm
Depth	Battery: 35 mm Circuit: 40.5 mm
Net Weight	0.46 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	850 °C
Standards	IEC 695-2-1 EN 61347-2-7 IEC 34-50 IEC 50-11 EN 60695-2-10 EN 60924

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8.3 cm
Package 1 Length	26.5 cm
Package 1 Weight	500 g

Contractual warranty

Warranty	18 months
----------	-----------