

Product data sheet

Specifications



RelayAux - single phase trip circuit supervision relay - 2 C/O - 24 V DC

REL91320

Main

Range Of Product	RelayAux
Product Or Component Type	Trip circuit supervision relay
Network Number Of Phases	1 phase
[Uc] Control Circuit Voltage	24 V DC (- 25 % + 10 % Un)
Status Led	With
Local Signalling	LED

Complementary

Contacts Type And Composition	2 C/O
Insulation Resistance Measurements	> 100 MOhm at 500 V DC conforming to IEC 60255-5
[Uimp] Rated Impulse Withstand Voltage	5 kV during 1.2/50 µs conforming to IEC 60255-5
Contacts Material	AgNi
Permanent Current	8 A
Instantaneous Current	15 A: instantaneous 15 A during 4 s
Maximum Making Capacity	15 A during 4 s
Mechanical Durability	10000000 cycles
Consumption In Permanence (Un)	1.35 W
Drop-Out Time	500 ms
Maximum Contact Resistance	30 mOhm
Mechanical Robustness	Shocks 11 ms (5 gn) conforming to IEC 60068-2-27 Bumps 16 ms (10 Gn) conforming to IEC 60068-2-29
Height	50.4 mm
Width	42.5 mm
Depth	96.6 mm
Net Weight	0.1 kg

Environment

Dielectric Strength	2 kV 50 Hz 1 min conforming to IEC 60255-5
---------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electromagnetic Compatibility	Conducted and radiated emissions criteria A conforming to EN 55022 Conducted and radiated emissions criteria B conforming to EN 55022 Electrostatic discharge - test level: 15 kV level 4 (air discharge) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV level 4 (contact discharge) conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test - test level: 10 V/m, 80 MHz...1 GHz level 3 conforming to IEC 61000-4-3 Radiated radio-frequency electromagnetic field immunity test - test level: 10 V/m, 80 MHz...1 GHz level 3 conforming to ENV 50204 Electrical fast transient/burst immunity test - test level: 4 kV, 5 kHz level 4 (1 min) conforming to IEC 61000-4-4 Surge immunity test - test level: 2 kV level 3 (common mode) conforming to IEC 61000-4-5 Surge immunity test - test level: 1 kV level 3 (differential mode) conforming to IEC 61000-4-5 Conducted RF disturbances - test level: 10 V, 0.15...80 MHz level 3 conforming to IEC 61000-4-6 Magnetic field at power frequency - test level: 100 A/m level 5 (continuous) conforming to IEC 61000-4-8 Magnetic field at power frequency - test level: 1000 A/m level 5 (2 s) conforming to IEC 61000-4-8 Damped oscillating waves - test level: 2.5 kV, 1 MHz level 3 (common mode) conforming to IEC 60255-22-1 Damped oscillating waves - test level: 1 kV, 1 MHz level 3 (differential mode) conforming to IEC 60255-22-1
Environmental Characteristic	Exposure to cold in operation conforming to IEC 60068-2-1 Exposure to cold in storage conforming to IEC 60068-2-1 Continuous exposure to damp heat in storage 56 d (93 %) conforming to 40 °C conforming to IEC 60068-2-78 Salt mist in storage conforming to ISO 9227 Exposure to dry heat in operation conforming to IEC 60068-2-2 Exposure to dry heat in storage conforming to IEC 60068-2-2
Vibration Resistance	1 gn (f = 58...150 Hz) conforming to IEC 60068-2-1 +/- 0.075 mm (f = 10...58 Hz) conforming to IEC 60068-2-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...70 °C
Fire Resistance	850 °C during 30 s
Operating Altitude	< 2000 m
Directives	72/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility 92/31/EEC - electromagnetic compatibility 93/68/EEC - low voltage directive
Product Certifications	UL listed file E322124 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	5.0 cm
Package 1 Length	2.3 cm
Package 1 Weight	270.0 g

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Reach Regulation		REACH Declaration
<hr/>		
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration
<hr/>		