


Product data sheet

Specifications



PratiKa wander socket for container - 32 A - 3P+E - 400..440 V AC - IP 67

PKY32M7C4

Main

Range Of Product	PratiKa
Product Or Component Type	Wander socket
Device Short Name	PratiKa socket
Plug, Socket Category	Low voltage
Industrial Socket Type	Fast
Poles Description	3P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

[In] Rated Current	32 A
[Ue] Rated Operational Voltage	400...440 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	3 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: brass
Connections - Terminals	Fast connection
Cable Cross Section	2.5...6 mm²
Cable Outer Diameter	11.5...21 mm
Net Weight	0.309 kg
Height	99 mm
Width	99 mm
Depth	164 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Standards	EN 60309-1 EN 60309-2
Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	50 % at 40 °C
	70 % at 30 °C
	90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	9.5 cm
Package 1 Length	15.2 cm
Package 1 Weight	270.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations