



Main

Range	Pragma
Product or component type	Enclosure
Enclosure type	Distribution enclosure
Width	366 mm wall 396 mm outside
Height	780 mm wall 810 mm outside
Depth	41 mm outside 86 mm wall
Nb of 18 mm modules per row	13
Nb of horizontal rows	4
Electrical insulation class	Class II Double insulation
Provided equipment	Marking kit (1) Identification label (1) Terminal block (1) Blanking plate strip (1)
Type of door	Opaque

Complementary

Enclosure mounting	Flush
9 mm pitches	26
Total number of 18 mm modules	52
Power dissipation in W	76 W
[In] rated current	90 A
Type of rail	DIN
Cable entry	Cable or tube Removable plates Side pre-cutouts
Number of terminal blocks	1 earth terminal block with 26 Quick outgoers
Distribution block outgoers	2 x 25 mm ² for earth 24 x 6 mm ² for earth
Enclosure material	Back part : technoplastic Door : technoplastic Front face : technoplastic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Door : white (RAL 9016) Enclosure : white (RAL 9016) Front face : grey (RAL 7004)
--------	---

Environment

Fire resistance	Back part : 650 °C conforming to IEC 60695-2-1 Front face : 650 °C conforming to IEC 60695-2-1 Door : 650 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
IK degree of protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C
Standards	EN 60439-3 EN 60695-2-11 IEC 60439-3 IEC 60529 IEC 60695-2-11 IEC 60947-7-1 IEC 62262

Contractual warranty

Warranty period	18 months
-----------------	-----------