

# Product data sheet

Specifications



## Séquence5 - Top/Class - shaver socket - 3 m - Chrome

S800064CV

! Discontinued on: Jul 26, 2021

! End-of-service on: Aug 19, 2021

! Discontinued

### Main

|                           |                              |
|---------------------------|------------------------------|
| Range                     | Sequence5                    |
| Product Or Component Type | Shaver socket                |
| Product Compatibility     | Uninterruptible power supply |
| Device Presentation       | Complete product             |
| Rated Power In Va         | 20 VA                        |
| Input Voltage             | 240 V 50 Hz                  |
| Output Voltage            | 115...240 V AC 50/60 Hz      |
| Fixing Mode               | By screws                    |
| Colour Tint               | Chrome                       |

### Complementary

|                                       |  |
|---------------------------------------|--|
| Connections - Terminals               | Screw terminals  |
| Cable Cross Section                   | 4 mm² flexible cable<br>4 mm² rigid cable  |
| Minimum Load Breaking Capacity        | 100 operations 1.25 In and 1.1 Un, cos phi = 0.6   |
| Electrical Durability                 | 10000 cycles, cos phi = 0.8  |
| Insulation Resistance                 | > 5 MOhm at 500 V  |
| Dielectric Strength                   | 2000 V   |
| Material                              | Metal  |
| Surface Finish                        | Glossy   |
| Quantity Per Set                      | Set of 1 box   |
| Standards                             | NOM-003-SCFI-2000<br>BS 546:1950<br>UNE 20315-1-2<br>IEC 60884-1<br>SI 32<br>NFC 61-314<br>BS 1363-1<br>VDE 0620-1 |
| Ambient Air Temperature For Operation | 15...30 °C   |
| Ambient Air Temperature For Storage   | 0...35 °C  |
| Height                                | 80 mm  |
| Width                                 | 120 mm   |
| Depth                                 | 51.5 mm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                 |          |
|-----------------|----------|
| Embedding Depth | 41 mm    |
| Net Weight      | 1.046 kg |

## Environment

|                              |   |
|------------------------------|---|
| Ik Degree Of Protection      | IK01  |
| Ip Degree Of Protection      | IP20  |
| Environmental Characteristic | Liquid soap<br>UV resistant<br>Window-cleaning fluid<br>Oil<br>Alcohol<br>Bleach<br>Acetone<br>Petrol |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 6 cm   |
| Package 1 Width              | 14 cm  |
| Package 1 Length             | 20 cm  |
| Package 1 Weight             | 1118 g |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

---