

Product data sheet

Characteristics

S800512BM

Séquence5 - rotary dimmer - 2-way switch - R,L -
4...400 VA - Bronze



Main

Range of product	Sequence5
Product or component type	Rotary dimmer
Device presentation	Complete product
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1
Dimmer additional information	2-wire connection

Complementary

Device mounting	Flush
Switch function	2-way
Fixing mode	By screws
Colour tint	Bronze
Surface finish	Glossy
Dimmer application	Capacitive load Inductive load Ohmic load
Dimmer control	Dimming
Load type	230 V AC incandescent lamp 4...400 W 230 V AC halogen lamp 4...400 W LED lamp 4...200 VA LED lamp 4...40 VA Low voltage halogen lamp with electronic transformer 4...400 VA Low voltage halogen lamp with ferromagnetic transformer 4...400 VA
[Ue] rated operational voltage	230 V AC 50 Hz
Protection type	Circuit breaker protection
Number of terminals	4 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1.5...2.5 mm ² solid cable(s) 1.5...2.5 mm ² stranded cable(s) 1.5...2.5 mm ² flexible cable(s)
Wire stripping length	8 mm
Height	80 mm
Width	80 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	51 mm
Embedding depth	29 mm
Product weight	0.245 kg

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	2004/108/EC 2006/95/EEC EN 60669-2-1
Product certifications	NF Aenor
IK degree of protection	IK02
IP degree of protection	IP20