


Product data sheet

Specifications



Sedna - double USB charger 2.1 A - titanium

SDN2710268

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

Range Of Product	Sedna
Product Or Component Type	USB charger
Integrated Connection Type	2 USB 2.0 port 5 V DC, maximum load current: 2.1 A

Complementary

Device Application	Charger
Device Mounting	Flush
Device Presentation	Mechanism with fixing frame
Surface Treatment	Untreated
Number Output Current	2.1 A
Fixing Mode	By screws
Type Of Packing	Flow-pack
[Ue] Rated Operational Voltage	100...240 V AC +/- 10 % at 50/60 Hz
Power Consumption In W	0.1 W
Nominal Output Power	10.5 W
Input Power	12 W
Service Life In Hours	30000 h 10.5 W
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Protection Type	Short-circuit protection
Number Of Terminals	2 screw terminals
Clamping Connection Capacity	2 x 0.75...2 x 2.5 mm ² for rigid cable(s) 2 x 0.75...2 x 2.5 mm ² for flexible cable(s) 2 x 0.75...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	8 mm
Product Compatibility	Mobile/tablet Mac iOS Mobile/tablet Windows
Height	71 mm
Width	71 mm
Depth	37 mm
Embedding Depth	30.8 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Standards	ETSI EN 301 489-4
Directives	2006/95/EC - low voltage directive
Product Certifications	EAC
Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	6.3 cm
Package 1 Length	12.9 cm
Package 1 Weight	113.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	36
Package 2 Height	18.5 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.47 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations