


Product data sheet

Specifications



Sedna - double socket-outlet with side earth - 16A, beige

SDN3000647

 **Discontinued on:** Dec 31, 2022

 **Discontinued**

Main

Range Name	Sedna
Function	Socket-outlet
Delivery Form	Complete product
Type Of Packing	Flow-pack and cardboard with eurohole
Outlet Poles Configuration	2P + E
Outlet Standard Description	Side earth
Rated Current	16 A at 250 V AC
Market Segment	Residential Small commercial

Complementary

Wire Stripping Length	11 mm
Surface Finish	Glossy
Material Of Visible Parts	ASA + PC
Wire Structure	Solid stranded Flexible Rigid
Terminal Capacity	2 cable(s) 2.5 mm ²
Kind Of Terminals	Lift terminals
Power Range	3680 W

Environment

Ip Degree Of Protection	IP20
Product Certifications	EAC

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	8.4 cm
Package 1 Length	12 cm
Package 1 Weight	87 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations