

# Product data sheet

Specifications



## Cover frame, Odace Touch, 2 gangs, aluminium

S530814J1

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                           |             |
|---------------------------|-------------|
| Range Of Product          | Odace       |
| Aesthetic Name            | Touch       |
| Product Or Component Type | Cover frame |
| Number Of Gangs           | 2 gangs     |
| Installation Direction    | Vertical    |
| Distance Between Centers  | 57 mm       |
| Type Of Frame             | Double      |
| Type Of Packing           | Flow-pack   |

### Complementary

|                               |   |
|-------------------------------|---|
| Device Mounting               | Flush   |
| Fixing Mode                   | Clip-in   |
| Colour Tint                   | Aluminium croco   |
| Side Color                    | Aluminium   |
| Surface Finish                | Brushed   |
| Material                      | Aluminium<br>PC (polycarbonate)   |
| Height                        | 142 mm  |
| Width                         | 85 mm   |
| Depth                         | 10 mm   |
| Net Weight                    | 0.01924 kg  |
| Resistance To Chemical Agents | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

### Environment

|                                       |            |
|---------------------------------------|------------|
| Ambient Air Temperature For Storage   | -5...50 °C |
| Ambient Air Temperature For Operation | 5...45 °C  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |   |
|-------------------------|---|
| Standards               | NBN C 61-112-1<br>UNE 20315-1-1<br>2006/95/EEC<br>NF C 61-314<br>EN 60669-1 |
| Product Certifications  | N<br>NF   |
| Ik Degree Of Protection | IK04  |
| Ip Degree Of Protection | IP21D   |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 1.0 cm   |
| Package 1 Width              | 8.5 cm   |
| Package 1 Length             | 14.5 cm  |
| Package 1 Weight             | 30.0 g   |
| Unit Type Of Package 2       | BB1      |
| Number Of Units In Package 2 | 5        |
| Package 2 Height             | 5.8 cm   |
| Package 2 Width              | 9.0 cm   |
| Package 2 Length             | 37.0 cm  |
| Package 2 Weight             | 210.0 g  |
| Unit Type Of Package 3       | S03      |
| Number Of Units In Package 3 | 60       |
| Package 3 Height             | 30.0 cm  |
| Package 3 Width              | 30.0 cm  |
| Package 3 Length             | 40.0 cm  |
| Package 3 Weight             | 2.976 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |