


Product data sheet

Specifications



Séquence5 - dolly switch - 2-way - 10 AX - Bronze

S800204BM

 **Discontinued on:** Sep 30, 2021

 **Discontinued**

Main

Range Of Product	Sequence5
Product Or Component Type	Switch
Device Presentation	Complete product
Switch Additional Information	With internal power connection
Switch Application	On/off switching
Type Of Packing	Box
Quantity Per Set	Set of 1
Sale Per Indivisible Quantity	1

Complementary

Device Mounting	Flush
Switch Function	2-way
Number Of Rocker	1
Actuator	Small dolly rocker
Fixing Mode	By screws
Colour Tint	Bronze
Surface Finish	Glossy
Rated Current	10 AX at 250 V AC 50 Hz
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un with $\cos \varphi = 0.3$
Service Life In Cycles	20000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Electrical Durability	20000 cycles at ON and OFF at rated voltage with $\cos \varphi = 0.6$
Number Of Terminals	3 screwless terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for rigid cable(s) 1 x 1.5...2 x 2.5 mm ² for flexible cable(s) 1 x 1.5...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	12 mm
Material	Metal
Height	80 mm
Width	80 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	35 mm
Net Weight	0.235 kg

Environment

Ambient Air Temperature For Storage	-5...50 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	5...35 °C
Standards	EN 60669-1 2006/95/EEC
Product Certifications	LCIE: CCA-FR_598285B LCIE: NF 604950 NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Oil Alcohol Petrol UV resistant Bleach Acetone Liquid soap Window-cleaning fluid

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	10 cm
Package 1 Length	12.5 cm
Package 1 Weight	270 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
