



### Main

|                               |                     |
|-------------------------------|---------------------|
| Range of product              | Sequence5           |
| Product or component type     | USB charger         |
| Device presentation           | Complete product    |
| Colour tint                   | Copper              |
| Surface finish                | Glossy              |
| Provided equipment            | Supplied with claws |
| Type of packing               | Box                 |
| Quantity per set              | Set of 1            |
| Sale per indivisible quantity | 1                   |

### Complementary

|                                |   |
|--------------------------------|---|
| Device mounting                | Flush   |
| Connector type                 | USB 2.0   |
| [Ue] rated operational voltage | 100...240 V AC 50/60 Hz   |
| Power consumption in W         | < 0.1 W   |
| Input power                    | 7.5 W   |
| Output voltage                 | 5 V DC 1 A  |
| Material                       | Metal   |
| Protection type                | Short-circuit protection  |
| Number of terminals            | 2 screw terminals   |
| Shape of screw head            | Pozidriv No 1   |
| Clamping connection capacity   | 1.5...2.5 mm <sup>2</sup> rigid<br>1.5...2.5 mm <sup>2</sup> flexible<br>1.5...2.5 mm <sup>2</sup> stranded |
| Wire stripping length          | 8 mm  |
| Fixing mode                    | By screws   |
| Height                         | 80 mm   |
| Width                          | 80 mm   |
| Depth                          | 40 mm   |
| Embedding depth                | 37 mm   |
| Product weight                 | 0.798 kg  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -5...40 °C  |
| Ambient air temperature for storage   | -5...50 °C  |
| Standards                             | EN 60950-1<br>EN 62684<br>EU directive 2002/95/EC<br>WEEE directive 2002/96/EC<br>ETSI EN 301 489-4 |
| Electrical insulation class           | Class II  |
| Environmental characteristic          | REACH Regulation (EC) No 1907/2006  |
| IK degree of protection               | IK04  |
| IP degree of protection               | IP20  |