



### Main

Range	Sequence5
Product or component type	Multi-services socket
Device mounting	Flush
Fixing mode	By screws
Colour tint	Copper
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1

### Complementary

Device presentation	Complete product
Outlet poles configuration (Socket-Outlet)	2P + E with shutters
Outlet standard description (Socket-Outlet)	Pin earth
Outlet standard (Socket-Outlet)	French
Rated current (Socket-Outlet)	16 A 250 V AC 50 Hz
Dielectric strength (Socket-Outlet)	2000 V
Service life in cycles (Socket-Outlet)	5000 cycles
Electrical durability (Socket-Outlet)	5000 cycles
Number of terminals (Socket-Outlet)	3
Clamping connection capacity (Socket-Outlet)	1 x 1.5...2 x 4 mm <sup>2</sup> rigid 1 x 1.5...2 x 4 mm <sup>2</sup> stranded 1 x 1.5...2 x 4 mm <sup>2</sup> flexible
TV connector (TV)	Male IEC 9.52 mm
Path attenuation (TV)	1.5 dB TV 5...1800 MHz 2.5 dB TV 1800...2150 MHz
Type of cable (TV)	Coaxial
Shape of screw head	TV module pozidriv No 1 Socket-outlet pozidriv No 1
Cable outer diameter	TV module 7 mm
Device composition	Socket-outlet ASA + PC mechanism cover Socket-outlet PC (polycarbonate) GF10 FR casing TV module zinc alloy casing

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surface finish	Glossy
Width	160 mm
Height	80 mm
Depth	39.5 mm
Embedding depth	35 mm
Product weight	0.548 kg

## Environment

IK degree of protection	IK04
IP degree of protection	IP21 D
Ambient air temperature for operation	Socket-outlet 5...35 °C TV module 5...45 °C
Ambient air temperature for storage	-5...50 °C
Standards	EN 50083-4 NF C 61-314
Product certifications	NF LCIE NF 603415A
Environmental characteristic	Acetone Alcohol Ammonia Bleach Liquid soap Oil Petrol UV resistant Window-cleaning fluid
Environmental health and issues	Halogen free