



Main

Range	Sequence5
Product type	RJ45 network socket
Type of footprint	S-One
Device presentation	Integrated one piece design
Performance category	6
Compatible LAN cable types	F/FTP SF/UTP U/FTP S/FTP F/UTP
Supported applications	1000BASE-T
Protocols	PoE+ (Power over Ethernet) VoIP (Voice IP)
Material and colour	Bronze (metal)
Surface finish	Glossy
Quantity per set	Set of 1
Width	80 mm
Height	80 mm
Depth	37 mm

Complementary

Frequency range	0...250 MHz
Protection type	Metallic 360° self adjusting + drain wire contact Integrated short circuit barrier
Voltage proof	1000 V AC/DC, peak, between contacts 1500 V AC/DC, peak, between contacts and shield
Current rating	≤ 1.5 A @25 °C
Insulation resistance	Initial insulation resistance : ≤ 500 MOhm @100 V DC
Electrical resistance	≤ 20 mOhm
Transfer impedance	≤ 0.2 Ohm at 10 MHz ≤ 0.1 Ohm at 1 MHz ≤ 1.6 Ohm at 80 MHz
Coupling attenuation	≥ 45 dB from 30...100 MHz $\geq 85 - 20 \times \log(f)$ dB from 100...1000 MHz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Transverse conversion loss	>= 68 - 20 x log(f) dB from 1...250000 kHz >= 50 dB
Contact pins	8 pins in copper alloy and gold plated (IEC 60603-7)
Durability	>= 750 cycles
IDC wire diameter	AWG 23...AWG 24
Insulation diameter (wire)	0.9...1.4 mm
Pulling force	50 N during 60 s
Applicable standards	IEC 60603-7-5 ISO/IEC 11801 amd2:2010 ANSI/TIA-568-C.2 ISO/IEC 11801 Ed2.1
Embedding depth	31 mm
Product weight	0.207 kg

Environment

Operational temperature range	-40...70 °C
Environmental characteristic	REACH PEP (Energy depletion)
Climatic category	40/070/21 (21 days)